

TECHSPEC® 50mm Diameter, 700nm Cut-On SWIR Longpass Filter



Stock **#86-447** **8 In Stock**

⊖ 1 ⊕ **A\$262⁴⁰**

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-9 | A\$262.40 each |
| Qty 10-25 | A\$236.80 each |
| Qty 26-49 | A\$225.60 each |
| Need More? | Request Quote |

Product Downloads

General

Longpass Filter **Type:**

Physical & Mechanical Properties

50.00 **Diameter (mm):**

1.20 ±0.15 **Thickness (mm):**

Dimensional Tolerance (mm):
+0.0/-0.2

Optical Properties

Cut-On Wavelength (nm):
700.00

Substrate:
BOROFLOAT®

Coating:
Traditional Coated

Rejection Wavelength (nm):
350 - 685

Surface Quality:
80-50

Transmission Wavelength (nm):
710 - 2500

Cut-On Wavelength (µm):
0.7

Coating Specification:
T_{avg} <0.5% @ 350 - 685nm
T_{avg} >85% @ 900 - 1700 nm
T_{avg} >70% @ 710 - 900 nm and 1700 - 2500nm

Wavelength Range (nm):
350 - 2500

Surface Flatness (P-V):
4 - 6λ

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

REACH 241:
Compliant

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Block Visible Wavelengths
- Ideal for Machine Vision Applications
- Can Be Used as Cold Mirrors
- Additional [Longpass Edge Filters](#) Available

Designed to pass short-wave infrared (SWIR) wavelengths while blocking visible light, TECHSPEC® SWIR Longpass Filters are ideal for increasing the image quality of InGaAs cameras in a variety of machine vision applications. These longpass edge filters are offered in multiple sizes and cut-on wavelengths. TECHSPEC SWIR Longpass Filters can also be used as extended cold mirrors to eliminate damage or adverse effects caused by heat build-up.

Technical Information



Compatible Mounts

