

# 56 PC Gauge Block Set, Metric, Rectangular, Steel, AS-1 Grade

See More by [Mitutoyo](#)



Stock **#78-374** **1 In Stock**

-

1

+

A\$3,664<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | A\$3,664.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

|                   |
|-------------------|
| Product Downloads |
|-------------------|

## SPECIFICATIONS

### General

516-955-26

Model Number:

Note:  
Contains the following blocks:  
1 Block: 0.5mm  
9 Blocks: 1.001-1.009 (.001mm)  
9 Blocks: 1.01-1.09mm (.01mm)

9 Blocks: 1.1-1.9mm (.1mm)  
24 Blocks: 1-24mm (1mm)  
4 Blocks: 25-100mm (25mm)

|                       |                             |
|-----------------------|-----------------------------|
| Metric                | System of Measurement:      |
|                       |                             |
| 56                    | Number of Blocks:           |
| Steel                 | Construction Material:      |
|                       |                             |
| Material Properties   |                             |
| AS-1                  | Grade:                      |
| Regulatory Compliance |                             |
| View                  | Certificate of Conformance: |

## PRODUCT DETAILS

- Available in Steel and Ceramic Block Sets
- Rectangular Base for Accurate Wringing
- Includes Inspection Certificate

Mitutoyo Gauge Block Sets are highly accurate calibration tools for manufacturing quality control on thin dimensional parts and manufacturing traceability on standard-sized pieces. Available in different grades, sizes, and steps, these gauge blocks feature exceptional flatness and surface roughness. These gauge blocks are made from high-quality, temperature-stable steel or ceramic providing increased durability and resistance to wear. Mitutoyo Gauge Block Sets are ideal for a range of measurement and calibration applications such as cutting tool positioning, inspection of depth micrometers, and angle measurement with a sign bar.