

# 5mm Diameter, Outdoor, Hydrophobic Window

See More by [SCHOTT Optical Components](#)



Stock **#34-522** 20+ In Stock

-

1

+

A\$133<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | A\$133.60 each                |
| Qty 6-25       | A\$120.00 each                |
| Qty 26-99      | A\$113.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |        |
|----------------------------------|--------|
| Protective Window                | Type:  |
| Outdoor                          | Note:  |
| Physical & Mechanical Properties |        |
| Protective as needed             | Bevel: |

|                  |                          |
|------------------|--------------------------|
| 90.00            | Clear Aperture (%):      |
| 4.50             | Clear Aperture CA (mm):  |
| 5.00 +0.00/-0.25 | Diameter (mm):           |
| 1.10 ±0.1        | Thickness (mm):          |
| Fine Ground      | Edges:                   |
| 480.00           | Knoop Hardness (kg/mm²): |
| 0.20             | Poisson's Ratio:         |
| 64               | Young's Modulus (GPa):   |

|                                      |                                        |
|--------------------------------------|----------------------------------------|
| Optical Properties                   |                                        |
| 65.41                                | Abbe Number (v <sub>d</sub> ):         |
| Hydrophobic (425-675nm)              | Coating:                               |
| R <sub>avg</sub> <0.5% @ 425 - 675nm | Coating Specification:                 |
| 1.472                                | Index of Refraction (n <sub>d</sub> ): |
| BOROFLOAT®                           | Substrate:                             |
| 80-50                                | Surface Quality:                       |
| 425 - 675                            | Wavelength Range (nm):                 |


|                                 |                                                              |
|---------------------------------|--------------------------------------------------------------|
| Material Properties             |                                                              |
| 3.25                            | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
| Water: 90 - 110<br>Oil: 75 - 80 | Contact Angle (°):                                           |
| 2.23                            | Density (g/cm³):                                             |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 247:                  |


## Product Details

- Oil and Water Repellent Coating
  - Ideal for Industrial and Harsh Environments
  - AR Coated for <0.5% Reflection in the Visible Spectrum
- Hydrophobic Windows are designed to repel oil (oleophobic) and other liquids (hydrophobic), facilitating cleaning and ensuring maximum transmission of incident light. Hydrophobic treated surfaces cause liquids to form droplets on contact rather than be absorbed or spread across the surface of the optic. Hydrophobic Windows feature anti-reflection coatings to provide less than 0.5% reflection per surface from 425 – 675nm. These windows are ideal for harsh environments, portable handheld devices, or biometric measurement devices.
- Indoor Hydrophobic Windows are ideal for applications where cleaning or abrasion is expected while Outdoor Hydrophobic Windows provide better performance both at elevated temperatures and under direct UV light exposure.

## Technical Information



Hydrophobic Window Reflectivity Curve



Hydrophobic Window Transmission Curve

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts