


[See all 10 Products in Family](#)

6mm Dia. x 9mm FL, Small Diameter Plastic Aspheric Lens



Stock **#36-627** [CONTACT US](#)

-

1

+

A\$54⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$54.40 each
Qty 11-49	A\$44.80 each
Need More?	Request Quote

Product Downloads

General	
Aspheric Lens	Type:
Physical & Mechanical Properties	
6.00 ±0.20	Diameter (mm):
5.00	Clear Aperture CA (mm):

2.94	Edge Thickness ET (mm):
4.00 ±0.20	Center Thickness CT (mm):
Protective as needed	Bevel:

Optical Properties

9.00 @ 550nm	Effective Focal Length EFL (mm):
0.33	Numerical Aperture NA:
6.16	Back Focal Length BFL (mm):
Acrylic V825	Substrate: ☐
±1.5	Focal Length Tolerance (%):
550	Aspheric Design Wavelength (nm):
Uncoated	Coating:
60-40	Surface Quality:
1.51	f##:
400 - 1500	Wavelength Range (nm):
Infinite	Conjugate Distance:

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Small Diameter Eases OEM Integration
 - High Numerical Apertures
 - Ideal for Medical and Diagnostic Instrumentation
- Small Diameter Plastic Aspheric Lenses are designed with OEM integration in mind. The small diameters, lightweight materials, and high numerical apertures make these lenses ideal for medical devices, diagnostic instrumentation, or wearable applications. Full prescription data is available to assist in design integration.
- Note:** For custom coating requirements, please [contact us](#).

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts