

[See all 24 Products in Family](#)

Flea3/Grasshopper3 8-pin GPIO Hirose Connector Cable, 4.5m

See More by [Teledyne FLIR](#)



Flea3/Grasshopper3 8-pin GPIO Hirose Connector Cable, 4.5m, #88-060



Stock **#88-060** **3 In Stock**

- 1 + A\$91²⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$91.20 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Camera Accessory **Type:**

Hardware & Interface Connectivity

Length of Cable (m):
4.5

Certificate of Conformance:

[View](#)

Product Details

- Feature High Resolution, High Sensitivity Sensors
- High Frame Rates Driven by USB 3.0 Interface
- Includes Image Capture Software and SDK



Teledyne
Authorized
Distributor

Teledyne FLIR IIS Grasshopper®3: Machine Vision area scan camera

The **Grasshopper®3** offers a cost-effective, powerful and easy-to-use alternative to Camera Link and dual GigE LAG solutions.

The **Grasshopper®3** camera line combines the benefits of CCD with the affordability and data throughput of either USB 3.0 or GigE interfaces. This high-performance camera model provides a range of characteristics with either CMOS or CCD sensors. Its FPGA and frame buffer-based architecture provides optimal reliability, a rich set of features, and a full image processing pipeline including color interpolation, gamma, and lookup table functionality.

Note: USB 3.0 cable (sold separately) is required for operation. Optional power supply ([#86-784](#)) available. Software available for [download](#). FLIR was previously known as Point Grey.

Features

- Compact form factor
- USB 3.0 models with resolutions from 2.3 to 12 Megapixel sensors
- GigE interface model at 2.3 Megapixel for high bandwidth performance
- Various high-resolution, large format CCD and CMOS sensor options
- Color transformation tools for true-to-life color
- GigE models feature PoE for simplified setup and maintenance
- Spinnaker SDK and code samples

Applications

- Factory automation
 - 3D Measurement
 - Flat Panel Inspection
 - Life science instrumentation
 - Biometrics kiosk solutions
 - Ophthalmology
 - Intelligent traffic systems
-