

**TECHSPEC® 800 - 1200nm, 25.2 x 35.6mm, Dichroic Shortpass Filter Kit (9 Filters)**



Stock #15-111 [CONTACT US](#)

A\$2,419<sup>20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$2,419.20 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

**Filters Included:**  
 Cut-off Wavelengths: [800nm](#), [850nm](#), [900nm](#),  
[950nm](#), [1000nm](#), [1050nm](#), [1100nm](#), [1150nm](#),  
[1200nm](#)

**Type:**  
 Shortpass Filter

**Number of Filters:**  
 9

**Physical & Mechanical Properties**

**Dimensions (mm):**  
 25.2 x 35.6

Length (mm):  
35.60

Width (mm):  
25.20

**Physical Durability:**  
Adhesion per MIL-PRF-13830B, Section C.4.5.12  
Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11  
Cleaning per MIL-C-48497A Section 4.5.4.2

## Environmental & Durability Factors

**Environmental Durability:**  
Humidity per MIL-STD-810H, Section 507.6  
Temperature per MIL-STD-810H, Section 501.7 and 502.7

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- Sharp Cut-Off Wavelength
- Broad Transmission and Reflection Ranges
- Available in a Range of Common Sizes

Our TECHSPEC® Dichroic Shortpass Filters are designed for a 45° angle of incidence. The rejected light is reflected at 90°, making these filters ideal for use in fluorescence applications or as spectral beamsplitters. The filters feature low polarization dependence, broad spectral ranges, and a precision fused silica substrate. TECHSPEC® Dichroic Shortpass Filters have a sharp cut-off wavelength and are available in a wide range of sizes for ease of system integration. These filters can be combined with TECHSPEC® Dichroic Longpass Filters to create custom bandpass filters.

**Note:** The chevron on the edge of the filter points towards surface S1 with the primary filter coating on which the light should be incident.

## Technical Information

