

8mm CA, Corning® Varioptic® V-PE Series Variable Focus and Astigmatism Liquid Lens Development Kit



Corning® Varioptic® V-PE Series Variable Focus Liquid Lenses



Stock **#74-503** NEW **4 In Stock**

-

1

+

A\$1,815⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,815.00 each
Need More?	Request Quote

Product Downloads

General

Development Kit	
Type:	
Development Kit	
Contents of Kit:	
Corning® Varioptic® V-PE-80R0-07 Lens USB-MUniversal (with V-PE connector and USB compatibility) USB-B to USB-A Cable Visalab Software Control Software Documentation Package (USB-Stick)	
D-V-PE-80R0-07	
Model Number:	
Typical Applications:	
Compact optical systems providing tunable power : Sphere, Cylinder and Axis	

Physical & Mechanical Properties

27.00 (packaged lens)	
Diameter (mm):	

8.0	Clear Aperture CA (mm):
7.80 (packaged lens)	Thickness (mm):
Optical Properties	
VS	Coating:
-12 to +12 diopter (Sphere Only) -6 to +6 diopter (Sphere using Cylinder) -5 to 0 diopter(Cylinder Only)	Focus Range (mm):
95 @ 587nm	Transmission (%):
300nm	Transmitted Wavefront Error, RMS:
Environmental & Durability Factors	
+10 to +40	Operating Temperature (°C):
-40 to +55	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Combine a Liquid Lens with Dedicated, Calibrated Driver Board
- Temperature Compensation and Response Time Optimization Features
- Sweep Mode for Continuous Imaging while Lens is in Motion
- [A-P Series Liquid Lenses](#) Also Available

Corning® Varioptic® A-PE & V-PE Series Variable Focus Liquid Lenses feature a variable focus liquid lens with a dedicated, calibrated driver board for enhanced performance, temperature compensation, and response time optimization. The driver board enables advanced features including temperature compensation algorithms, response time optimization for optical power changes, and sweep mode which acquires clear images while the liquid lens is still in motion. The V-PE Series expands on this technology with an 8-electrode design, enabling independent control of spheres at ±24 diopters of power, cylinders at ±5 diopters of power, and axis for astigmatism correction without any moving parts, ensuring silent, reliable operation. Corning® Varioptic® A-PE & V-PE Series Variable Focus Liquid Lenses are ideal for use in barcode readers, industrial inspection, medical imaging, and biometrics applications and are fully compatible with the [AF Explorer Camera](#) for plug-and-play operation. Development kits include lenses, drive electronics, cables, software, and a dedicated drive board for ease of use and simplifying integration into OEM systems.