

[See all 3 Products in Family](#)

# Basler ace2 a2A2840-67g5mUV Ultraviolet (UV) 5GigE Camera

See More by [Basler](#)



Basler ace2 Ultraviolet (UV) GigE Camera



Stock **#72-581** [CONTACT US](#)

-

1

+

A\$11,824<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | A\$11,824.00 each             |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

|                 |               |
|-----------------|---------------|
| UV              | Spectrum:     |
| General         |               |
| UV Camera       | Type:         |
| a2A2840-67g5mUV | Model Number: |
| Manufacturer:   |               |

|                                                               |                             |
|---------------------------------------------------------------|-----------------------------|
| Basler                                                        |                             |
| ace2                                                          | Camera Series:              |
| Physical & Mechanical Properties                              |                             |
| 36.3 x 29 x 29                                                | Dimensions (mm):            |
| <105                                                          | Weight (g):                 |
| Full                                                          | Housing:                    |
| Sensor                                                        |                             |
| Not Specified                                                 | Image Buffer:               |
| 2/3"                                                          | Sensor Format:              |
| 8.10                                                          | Resolution (Megapixels):    |
| 67.00                                                         | Frame Rate (fps):           |
| 2,856 x 2,848                                                 | Pixels (H x V):             |
| 2.74 x 2.74                                                   | Pixel Size, H x V (µm):     |
| 7.78 x 7.78                                                   | Sensing Area, H x V (mm):   |
| Sony IMX487                                                   | Imaging Sensor:             |
| Progressive Scan CMOS                                         | Type of Sensor:             |
| Global                                                        | Shutter Type:               |
| 8/10/12 Bit                                                   | Pixel Depth:                |
| Freely Programmable                                           | Exposure Time:              |
| Not Specified                                                 | Dynamic Range (dB):         |
| GigE Vision 2.0, GenICam                                      | Machine Vision Standard:    |
| Electrical                                                    |                             |
| 5.7                                                           | Power Consumption (W):      |
| Hardware & Interface Connectivity                             |                             |
| 5GigE (PoE)                                                   | Interface:                  |
| 5GigE, RJ45 with Screw Locks                                  | Connector:                  |
| Power over GPIO with <a href="#">#16-644</a>                  | Power Supply:               |
| 1 opto-coupled input line, 2 general purpose I/O (GPIO) lines | GPIOs:                      |
| Hardware Trigger (GPIO), Software Trigger, or Free-Run        | Synchronization:            |
| Back Panel                                                    | Interface Port Orientation: |
| 6-pin MB                                                      | GPIO Connector Type:        |
| Threading & Mounting                                          |                             |
| C-Mount                                                       | Mount:                      |
| 1/4-20 with Tripod Mount Adapter <a href="#">#16-641</a>      | Mounting Threads:           |
| Environmental & Durability Factors                            |                             |
| -10 to 50                                                     | Operating Temperature (°C): |
| -20 to +80                                                    | Storage Temperature (°C):   |
|                                                               |                             |
|                                                               |                             |

| Regulatory Compliance     |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
|                           |                             |
| <a href="#">View</a>      | Certificate of Conformance: |
|                           |                             |
|                           |                             |
| <a href="#">Compliant</a> | Reach 235:                  |
|                           |                             |

## Product Details

- UV (200 – 400nm) Imaging Capabilities with 8.1MP, 2.3" Sensor Format
- Compact Housing (29 x 29mm)
- Framerrates up to 67fps
- Powerful Computer Vision Feature Set with Beyond Features

Basler ace2 Ultraviolet (UV) Cameras integrate the Sony IMX487 Pregius S UV Sensor for high sensitivity in the 200 – 400nm UV spectrum. Featuring a compact 29 x 29mm form factor with 8.1MP sensor resolution, global shutter, and a 2/3" sensor format, these cameras are easily integrated into a variety of inspection applications. Basler ace2 Ultraviolet (UV) cameras integrate advanced Beyond software features for more efficient bandwidth use and more flexible scalability of pixel sizes, maximizing camera performance for demanding application requirements. These cameras are available in either GigE, 5GigE, or USB3.0 interfaces for high data throughput and are ideal for inspection applications operating within the ultraviolet (UV) wavelength such as wafer inspection, material sorting, security and surveillance, and solar inspection.