

[See all 22 Products in Family](#)

Blue 1" High Brightness LED Diffuse Axial Illuminator

See More by [Advanced Illumination](#)



Advanced Illumination Diffuse Axial LED Illuminators

Stock **#91-055** NEW **1 In Stock**

-

1

+

A\$1,128⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,128.00 each
Need More?	Request Quote

Product Downloads

General	
DL225-025470IC	Model Number:
LED Illuminator	Type of Illumination:
Advanced Illumination	Manufacturer:
Diffuse Axial	Geometry:
	Illumination Mode:

Physical & Mechanical Properties					
Physical Properties: - Molecular Weight: ~100,000 g/mol - Density: ~1.2 g/cm³ - Glass Transition Temperature (T_g): ~-10°C - Softening Point: ~180°C - Crystallinity: ~5% - Thermal Stability: Stable up to ~250°C	Mechanical Properties: - Tensile Strength: ~15 MPa - Elongation at Break: ~500% - Modulus: ~0.1 GPa - Impact Resistance: High - Compression Modulus: ~0.1 GPa - Creep Resistance: Moderate				

Aperture Size:

Color:

Wavelength (nm):

Working Distance (mm):

Connector:

Connector:

Power Supply:

Operating Temperature (°C):

Operating Temperature (°C):

Certificate of Conformance:

Certificate of Conformance:

Note: Required 24V power supply #66-855. **Accessories for Advanced Illumination products** are available and sold separately. Units cannot be intensity controlled.

