

[See all 7 Products in Family](#)

BWA-CAM NIR BWA Etalon Optic Assembly, 700nm-1200nm



Stock #89-728 **NEW** [CONTACT US](#)

⊖ 1 ⊕ A\$19,872⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | A\$19,872.00 each |
| Need More? | Request Quote |

Product Downloads

General

BWA-CAM-700-1200-R6-EO

Model Number:

Physical & Mechanical Properties

91.0 x 85.0 x 78.0

Dimensions (mm):

Optical Properties

700 - 1200

Spectral Range:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Real-Time Analysis of Laser Beam Caustic, M_f, Centroid, Ellipticity, and Astigmatism
- Compatible with CW and Pulsed Lasers with Single-Pulse Capability
- Ideal for Laser Development, Quality Control, and Optical System Monitoring
- Complies with ISO 11146 and ISO 13694

Haas Laser Technologies BWA-CAM M_f Analyzer Cameras offer real-time M_f measurement for continuous wave and pulsed lasers in UV, VIS, or IR wavelength configurations. Featuring a simple "one-button" calibration, this system is capable of delivering M_f measurements from a single pulse, making it ideal for dynamic or single-shot laser systems. Engineered in compliance with ISO 11146 and ISO 13694 standards, the BWA-CAM provides precise evaluation of critical spatial beam parameters, including M_f, beam profile, centroid, ellipticity, and astigmatism. Haas Laser Technologies BWA-CAM M_f Analyzer Cameras enable users to detect optical system degradation early and optimize laser performance for maximum quality and process stability. The modular design of the BWA-CAM supports a broad range of laser wavelengths and application environments, while its high measurement accuracy and real-time data acquisition make it an essential tool for R&D, manufacturing, and laser system diagnostics.