

[See all 7 Products in Family](#)

Coherent® High-Sensitivity Thermopile Sensor PS19Q 1098341 | 1W Max Power

See More by [Coherent®](#)



Coherent® High-Sensitivity Thermopile Sensors

Stock **#12-418** [CONTACT US](#)

⊖ 1 ⊕ **A\$3,328⁰⁰**

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | A\$3,328.00 each |
| Need More? | Request Quote |

Product Downloads

General

Model Number:
PS19Q Coherent Part Number: 1098341

Type:
[Meter required](#)

Linearity (%):
±1

Calibration Uncertainty (%):
1

Cooling Method:

Air

Response Time (s):

2

Note:

Includes a Wedged Quartz Window to Eliminate Thermal Background Radiation and Air Current Effects

Compatible Meters:

[#35-203](#), [#12-393](#), [#59-978](#),
[#88-411](#), [#66-277](#), [#88-412](#)

Maximum Incident Energy Density:

50mJ/cm² (10ns, 1064nm)

Physical & Mechanical Properties

Active Area Diameter (mm):

19

Optical Properties

Calibration Wavelength (nm):

514

Wavelength Range (nm):

300 - 2000

Wavelength Range (µm):

0.3 - 2

Sensor

Type of Sensor:

Thermopile

Electrical

Maximum Incident Power Density (kW/cm²):

0.5

Power Range:

100µW - 1W

Maximum Power (W):

1

Power Resolution:

10µW

Hardware & Interface Connectivity

Length of Cable (m):

2

Computer Interface:

DB-25

Environmental & Durability Factors

Thermally Stabilized:

Yes

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

Product Details

- Broad Spectral Range with High Sensitivity and High Resolution
- Large Active Area Sensors up to 19mm in Diameter
- Flat Broadband Output with No Saturation above 1mW/cm²

Coherent® High-Sensitivity Thermopile Sensors are designed to have a broad spectral response to accommodate an array of lasers with different wavelengths. The large active area and high resolution of these thermopile sensors allows for accurate measurements of low-power lasers. A range of models are available to meet specific needs relating to thermal stability, background radiation, and air current effect. Coherent® High-Sensitivity Thermopile Sensors are designed to accurately measure the laser power of small laser diodes, HeNe lasers, and small ion lasers. Unique to this design, these sensors will not saturate when laser power exceeds 1mW/cm².