

Coherent® Fan-Cooled Thermopile Sensor PM200F-50 1098472 | 200W Max Power

See More by [Coherent®](#)



Coherent® Fan-Cooled Thermopile Sensors

Stock **#12-402** 1 In Stock

-

1

+

A\$3,936⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$3,936.00 each
Need More?	Request Quote

Product Downloads

General	
1098472	Model Number:
Meter required	Type:
1	Calibration Uncertainty (%):
Fan	Cooling Method:
Compatible Meters:	

#35-203, #12-393, #59-978,
#88-411, #66-277, #88-412

Physical & Mechanical Properties

Active Area Diameter (mm):
50

Dimensions (mm):
102 x 102 x 114

Optical Properties

Calibration Wavelength (nm):
514

Wavelength Range (nm):
250 - 11000

Wavelength Range (µm):
0.25-11

Electrical

Power Resolution (W):
0.1

Power Range:
1W-200W

Maximum Power (W):
200

Minimum Power (W):
1

Hardware & Interface Connectivity

Computer Interface:
DB-25

Regulatory Compliance

RoHS 2015:
Exempt

Reach 224:
Contains SVHC(s)

Certificate of Conformance:
View

Product Details

- Designed to Measure Laser Power up to 300W
 - Ideal for Applications where Water-Cooling is Not Possible
 - Compact Size for Portability and Use in Field Applications
- Coherent® Fan-Cooled Thermopile Sensors are an excellent option for measuring high-powered lasers in environments where water-cooled thermopile sensors cannot be used. The fan cooling system makes it possible for these thermopile sensors to provide continuous power monitoring of lasers up to 300W. Additionally, the large 50mm aperture size allows for easy laser alignment for quick data acquisition. Coherent® Fan-Cooled Thermopile Sensors feature a compact size and easy set up procedure, making them ideal for use in the field or production testing. The high power resolution of these sensors ensures that accurate measurements are made for their large range of accepted laser powers.