

Complete 25.4mm Dia Longpass Filter Kit

See More by [Hoya](#)



Stock #66-136 **1 In Stock**

⊖ 1 ⊕ A\$2,078⁴⁰

ADD TO CART

| | |
|----------------|-------------------------------|
| Volume Pricing | |
| Qty 1+ | A\$2,078.40 each |
| Need More? | Request Quote |

Product Downloads

General

Filters Included :
All 37 Longpass Glass Color Filter Types

Type:
Longpass Filter

Physical & Mechanical Properties

Diameter (mm):
25.40

Bevel:
Protective as needed

Optical Properties

| | |
|-----------------|--|
| Colored Glass | Substrate: <input type="checkbox"/> |
| Uncoated | Coating: |
| Multiple Colors | Color: |

Regulatory Compliance

| | |
|---------------------------|------------------------------------|
| Compliant | Reach 181: |
| Exempt | RoHS 2015: |
| View | Certificate of Conformance: |

Product Details

- UV, VIS and IR Pass Ranges
- VIS Can Be Used for Color Bandpass
- Also Available [Mounted](#)

Hoya Colored Glass Longpass Filters feature a colored glass substrate. These filters are manufactured from substrates with inherently different absorption and transmission properties across a specific spectral region. Hoya Colored Glass Longpass Filters have UV, VIS, and IR pass ranges. A longpass filter has low transmission in the shortwave region (stopband) and high transmission in the longwave region (passband). These filters are also available in a [mounted](#) version.

Longpass Filter Kits

Longpass filter kits are available in three different options: UV-VIS, VIS, or VIS-NIR. Each kit contains 8 filters in either 12.5mm diameter, 1" diameter, or 2" square.

UV-VIS Kit Contains: WG 295, WG 305, WG 320, L 37, GG 400, GG 420, GG 435, GG 455

VIS Kit Contains: GG 475, GG 495, OG 515, OG 530, OG 550, OG 570, OG 590, RG 610

VIS-NIR Kit Contains: RG 630, RG 665, RG 695, RG 715, RG 780, RG 830, RG 850, RG 1000

Complete Filter Kits


Complete filter kits are available with 12.5mm diameter, 50.0mm diameter, 1" diameter, or 2" square filters. Each kit contains all 37 Longpass Glass Color Filter types.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

Filter Simulation Software

[Click here](#) to download HOYA's colored glass filter simulation software which can be used to calculate the internal transmittance and external transmission of each HOYA glass type. The software can simulate the performance of individual filters with user specified thickness.

Technical Information



| | |
|-------------|---|
| λ_s | limit of stopband: specified at 0.001% internal transmittance |
| λ_c | cut-off position: specified at 50% internal transmittance |
| λ_p | limit of the passband |
| t_{ip} | internal spectral transmittance at λ_p |
| ρ | density |
| T_g | transformation temperature |