

[See all 36 Products in Family](#)

## Dual Bandpass Blue-NIR Filter M25.5



Stock **#74-539** NEW **1 In Stock**

-

1

+

A\$385<sup>.60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | A\$385.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**Full Width-Half Max FWHM Range (nm):**  
45nm, 60nm ±5 nm

| General                              |                           |
|--------------------------------------|---------------------------|
| Dual Bandpass Mounted Imaging Filter | Type:                     |
| DB475/850-25.5                       | Model Number:             |
| Physical & Mechanical Properties     |                           |
| 27.5                                 | Outer Diameter (mm):      |
|                                      | Substrate Thickness (mm): |

|                       |                               |
|-----------------------|-------------------------------|
| 1mm                   |                               |
| Optical Properties    |                               |
| Blue-NIR              | Color:                        |
| 40/20                 | Surface Quality:              |
| ≥90%                  | Transmission (%):             |
| 460-490nm, 830-870nm  | Transmission Wavelength (nm): |
| Threading & Mounting  |                               |
| M25.5 x 0.50          | Filter Thread:                |
| 5.2                   | Mount Thickness (mm):         |
| Regulatory Compliance |                               |
| <a href="#">View</a>  | Certificate of Conformance:   |

## Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

**Note:** Other filter threads are available upon request.