

[See all 10 Products in Family](#)

## FLIR T300772ACC External Battery Charger for Ex Series



Stock #75-080 **NEW** [CONTACT US](#)

⊖ 1 ⊕ **A\$262<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1+	<b>A\$262.40</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

ExSeries **Model Number:**

#### Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Professional-Grade thermal imagers for Industrial Applications
- Rugged, Handheld Design for Field Use
- Wide Temperature Ranges up to 550°C (1022°F)
- Wi-Fi for Fast Image Transfer and Reporting

The FLIR ExSeries delivers professional-grade thermal imaging in a rugged, handheld design built for demanding field environments. Offering industry-leading infrared resolution and wide temperature measurement ranges up to 550°C (1022°F), the E5 Pro, E6 Pro, and E8 Pro models are ideal for maintenance, building inspections, electrical diagnostics, HVAC servicing, and industrial troubleshooting. The E5 Pro (160 × 120 resolution) provides reliable thermal imaging for general inspections, the E6 Pro (240 × 180 resolution) offers enhanced resolution for identifying smaller temperature variations, and the E8 Pro (320 × 240 resolution) delivers the highest clarity and thermal sensitivity for advanced diagnostics. Built-in Wi-Fi connectivity allows for fast image transfer, reporting, and data sharing directly from the field, streamlining workflows and improving efficiency. With precision thermal sensitivity down to 0.04°C on the E8 Pro, users can detect subtle heat patterns and prevent equipment failures before they occur. The ExSeries combines FLIR's trusted infrared technology with durability and portability, making it a top choice for professional thermal imaging applications.

Model	E5 Pro	E6 Pro	E8 Pro
Resolution	160 × 120 (19,200 pixels)	240 × 180 pixels (43,200 pixels)	160 × 120 (19,200 pixels)
Temp Range	-20°C to 400°C (-4°F to 752°F)	-20°C to 550°C (-4°F to 1022°F)	-20°C to 550°C (-4°F to 1022°F)
Thermal sensitivity	<0.06°C	<0.05°C	<0.04°C

**Accuracy:** ±2°C (±3.6°F) or ±2% of reading, for ambient temperature 10°C to 35°C (50°F to 95°F) and object temperature above 0°C (32°F)