

[See all 14 Products in Family](#)

LightPath 390017 | 3.5mm Dia., 0.72 NA, BBAR (3000-5000nm), Molded IR Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-718** **14 In Stock**

☐ [Other Coating Options](#)

-

1

+

A\$656⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$656.00 each
Qty 11-49	A\$590.40 each
Need More?	Request Quote

Product Downloads

General	
390017	Lightpath Lens Code:
Aspheric Lens	Type:

Physical & Mechanical Properties	
3.50 ±0.015	Diameter (mm):

2.60	Clear Aperture CA (mm):
0.72	Edge Thickness ET (mm):
1.10	Center Thickness CT (mm):

Protective as needed	Bevel:
----------------------	--------

Optical Properties

1.50 @ 2300nm	Effective Focal Length EFL (mm):
0.72	Numerical Aperture NA:

Black Diamond™ BD-2 (Ge ₂₆ Sb ₁₂ Se ₆₀)	Substrate: ☐
2300	Aspheric Design Wavelength (nm):

BBAR (3000-5000nm)	Coating:
R _{avg} <1.0% @ 3 - 5μm	Coating Specification:

80-50	Surface Quality:
0.69	f/#:

2.6023	Index of Refraction (n _d) @ 10μm:
2.5843	Index of Refraction (n _d) @ 14μm:

2.6210	Index of Refraction (n _d) @ 4μm:
2.6173	Index of Refraction (n _d) @ 5μm:

3000 - 5000	Wavelength Range (nm):
1.24	Working Distance (mm):

Infinite	Conjugate Distance:
2300	Focal Length Specification Wavelength (nm):

Material Properties

14.00	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
4.68	Density (g/cm ³):

70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 μm)	Thermo-optic coefficient dn/dT:
285.00	Transformation Temperature (°C):

Regulatory Compliance


Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Wavelength Range of 1.8 - 12μm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12μm. These lenses are available mounted or unmounted, in a variety of coating options.

Technical Information



,