


Laminated Wratten ND Filter 1.0 OD 48mm Dia



Stock #29-322 **8 In Stock**

1 A\$280^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	A\$280.00 each
Qty 11-25	A\$225.60 each
Need More?	Request Quote

Product Downloads
EO Spec Sheet

General

Type: Neutral Density Filter	Note: Supplied with protective film on both sides
-------------------------------------	--

Physical & Mechanical Properties

Diameter (mm): 48.00 +/- 0.3	
-------------------------------------	--

Optical Properties

Optical Density OD (Average): 1	Substrate: [ⓘ] Wratten 2 Filter, One-Side Laminated onto PMMA
Coating: Uncoated	Blocking Wavelength Range (nm): 400-700

Regulatory Compliance

Certificate of Conformance: View	
---	--

Product Details

- One-Side Laminated for Stability
- Available in 25mm and 48mm Sizes
- Kodak Filter No. 96
- Lightweight Alternative to Traditional Glass ND Filters

PMMA-Laminated Wratten ND Filters are ideal for light attenuation in image-forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. The laminated design offers additional stability and durability compared to traditional polyester/gelatin filters while remaining a lightweight alternative to traditional glass ND filters. These ND filters are available in 25mm or 48mm diameters and a thickness of 0.6mm. PMMA-Laminated Wratten ND Filters are uncoated and feature a blocking wavelength of 400 - 700nm with OD options of 0.1, 0.3, 0.5, 1.0, 2.0, and 3.0.