

Line Pattern Flat Light LFX3-100RD-PT-A

See More by [CCS](#)



Stock **#21-821** 1 In Stock

-

1

+

A\$4,800⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$4,800.00 each
Need More?	Request Quote

Product Downloads

General	
LFX3-100RD-PT-A	Model Number:
LED Illuminator	Type of Illumination:
CCS	Manufacturer:
Flat Light	Geometry:
Constant	Illumination Mode:

Physical & Mechanical Properties	
	Dimensions (mm): W 143 mm xD 143 mm xH 13.1 mm
	Weight (g): 400
Optical Properties	
	Color: Red
	Wavelength (nm): 632
Electrical	
	Power Consumption (W): 19
Hardware & Interface Connectivity	
	Input Voltage (V): 24
	Power Supply: Power Supply Required and Sold Separately. USA: #73-491 Europe: #73-491 Japan: #89-513 Korea: #33-773 China: #73-491
Regulatory Compliance	
	RoHS 2015: Exempt
	Reach 224: Contains SVHC(s)
	Certificate of Conformance: View

Product Details

- Detect Imperfections on Reflective Surfaces
- Line Pattern Projected Through Light Guiding Diffusion Plate
- Multiple Wavelengths and Working Distances Available

CCS Coaxial Line Pattern Flat Lights feature a line pattern on the surface of a light guiding diffusion plate which allows for the detection of minute bumps and dents on reflective surfaces. When integrated into a machine vision system, the image of the reflected line pattern highlights defects by breaking the continuity of the surface and distorting the line pattern. These flat lights are available with two pitch options, 1mm for shorter working distances and 2mm for longer working distances. CCS Coaxial Line Pattern Flat Lights are ideal for inspection of reflective surfaces such as mirrors, metal sheets, glass surfaces, and reflective films.

Technical Information

Two types of line patterns available


Select one to match your inspection conditions.

Imaging examples

Narrow pitch


1 mm type

LFX3-PT-A Series




2 mm type

LFX3-PT-B Series



Wide pitch



Example configuration (LFX3-100-PT)

Imaging example: Imaging the external appearance of metal plate

1