

# Coherent® Beam Position Thermopile Power Sensors 1168340 | 10mW-10W

See More by [Coherent®](#)



Stock #68-628 **5 In Stock**

⊖ 1 ⊕ A\$2,888<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$2,888.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

LM-10 Coherent Part Number: 1168340	<b>Model Number:</b>
Meterless	<b>Type:</b>
±1	<b>Linearity (%):</b>
±2	<b>Calibration Uncertainty (%):</b>
<b>Long Pulse Joule Mode Range (J):</b>	

0.5 - 10

Long Pulse Joule Mode Accuracy (%):

±3

Cooling Method:

Air

Maximum Incident Energy Density:

600mJ/cm<sup>2</sup> (10ns, 1064nm)

## Physical & Mechanical Properties

Active Area Diameter (mm):

16

## Optical Properties

Calibration Wavelength (nm):

10,600

Wavelength Range (µm):

0.25 - 10.6

## Sensor

Type of Sensor:

Quad Element Thermopile

## Electrical

Spectral Compensation Accuracy (%):

±1.5

Maximum Incident Beam Power (W):

10

Maximum Incident Power Density (kW/cm<sup>2</sup>):

6

Power Range:

10mW - 10W

Minimum Power (mW):

10

## Hardware & Interface Connectivity

Length of Cable (m):

2.5

Computer Interface:

USB

## Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

## Product Details

- Thermopile Detector Element for High Power Measurements
- Measure Beam Position on Detector Surface
- ISO 17025 Certified

Coherent® Beam Position Sensing Thermopile Power Sensors are all-purpose sensors designed to measure the average power or energy of a wide variety of continuous wave or pulsed lasers. Coherent Beam Position Sensing Thermopile Power Sensors utilize a quadrant thermopile detector disk to sense the position of the laser beam on the detector surface while measuring the laser power. Coherent thermopile sensors can operate across a wide range of input powers, and do not saturate.

**Note:** The LM-20 is designed for embedded use and must be mounted on a heat sink.