

Coherent® Beam Position Thermopile Power Sensors 1193300 | 100mW-100W

See More by [Coherent®](#)



Stock #88-420 **3 In Stock**

⊖ 1 ⊕ A\$4,232⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | A\$4,232.00 each |
| Need More? | Request Quote |

Product Downloads

General

| | |
|---|-------------------------------------|
| LM-100 Coherent Part Number: 1193300 | Model Number: |
| Meterless | Type: |
| ±1 | Linearity (%): |
| ±2 | Calibration Uncertainty (%): |
| Long Pulse Joule Mode Range (J): | |

0.5 - 50

Long Pulse Joule Mode Accuracy (%):

±3

Cooling Method:

Air

Maximum Incident Energy Density:

600mJ/cm² (10ns, 1064nm)

Physical & Mechanical Properties

Active Area Diameter (mm):

19

Optical Properties

Calibration Wavelength (nm):

10,600

Wavelength Range (µm):

0.25 - 10.6

Sensor

Type of Sensor:

Quad Element Thermopile

Electrical

Spectral Compensation Accuracy (%):

±1.5

Maximum Incident Beam Power (W):

100

Maximum Incident Power Density (kW/cm²):

6

Power Range:

100mW - 100W

Minimum Power (mW):

100

Hardware & Interface Connectivity

Length of Cable (m):

2.5

Computer Interface:

USB

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

Product Details

- Thermopile Detector Element for High Power Measurements
- Measure Beam Position on Detector Surface
- ISO 17025 Certified

Coherent® Beam Position Sensing Thermopile Power Sensors are all-purpose sensors designed to measure the average power or energy of a wide variety of continuous wave or pulsed lasers. Coherent Beam Position Sensing Thermopile Power Sensors utilize a quadrant thermopile detector disk to sense the position of the laser beam on the detector surface while measuring the laser power. Coherent thermopile sensors can operate across a wide range of input powers, and do not saturate.

Note: The LM-20 is designed for embedded use and must be mounted on a heat sink.