

Coherent® Beam Position Thermopile Power Sensors 1168339 | 10mW-3W

See More by [Coherent®](#)



Stock #68-627 3 In Stock

-

1

+

A\$2,832⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$2,832.00 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	
LM-3 Coherent Part Number: 1168339	
Type:	
Meterless	
Linearity (%):	
±1	
Calibration Uncertainty (%):	
±2	
Long Pulse Joule Mode Range (J):	

0.5 - 10	Long Pulse Joule Mode Accuracy (%):
±3	

Air	Cooling Method:
-----	-----------------

600mJ/cm ² (10ns, 1064nm)	Maximum Incident Energy Density:
--------------------------------------	----------------------------------

Physical & Mechanical Properties	
19	Active Area Diameter (mm):

Optical Properties	
10,600	Calibration Wavelength (nm):
0.25 - 10.6	Wavelength Range (µm):

Sensor	
Quad Element Thermopile	Type of Sensor:

Electrical	
±1.5	Spectral Compensation Accuracy (%):
3	Maximum Incident Beam Power (W):

6	Maximum Incident Power Density (kW/cm ²):
10mW - 3W	Power Range:

10	Minimum Power (mW):
----	---------------------

Hardware & Interface Connectivity	
2.5	Length of Cable (m):
USB	Computer Interface:

Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:

View	Certificate of Conformance:
------	-----------------------------

Product Details

- Thermopile Detector Element for High Power Measurements
- Measure Beam Position on Detector Surface
- ISO 17025 Certified

Coherent® Beam Position Sensing Thermopile Power Sensors are all-purpose sensors designed to measure the average power or energy of a wide variety of continuous wave or pulsed lasers. Coherent Beam Position Sensing Thermopile Power Sensors utilize a quadrant thermopile detector disk to sense the position of the laser beam on the detector surface while measuring the laser power. Coherent thermopile sensors can operate across a wide range of input powers, and do not saturate.

Note: The LM-20 is designed for embedded use and must be mounted on a heat sink.