


[See all 33 Products in Family](#)

Lucid Vision Labs Atlas™ ATL314S-CNL, Sony IMX342, 31.4MP, Color Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Atlas™ Power over Ethernet (PoE) 5GBASE-T (5GigE) Cameras

Stock **#25-130** **1 In Stock**

-

1

+

A\$9,808^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$9,808.00 each
Need More?	Request Quote

Product Downloads

Color	Spectrum:
General	
Color Camera	Type:
ATL314S-CNL	Model Number:
Lucid Vision Labs	Manufacturer:
	Camera Series:

Atlas™	
Physical & Mechanical Properties	
55 x 55 x 65 (excludes connectors)	Dimensions (mm):
240	Weight (g):
Housing:	
Full	
Sensor	
380MB	Image Buffer:
APS-C	Sensor Format:
Resolution (Megapixels):	
31.40	
Frame Rate (fps):	
17.90	
Pixels (H x V):	
6,464 x 4,852	
Pixel Size, H x V (µm):	
3.45 x 3.45	
Sensing Area, H x V (mm):	
22.30 x 16.74	
Imaging Sensor:	
Sony IMX342	
Type of Sensor:	
Progressive Scan CMOS	
Shutter Type:	
Global	
Pixel Depth:	
8/10/12 Bit	
Exposure Time:	
47µs - 10s (Normal); 2µs - 32µs (Short Mode)	
Dynamic Range (dB):	
0 - 48	
Machine Vision Standard:	
GigE Vision v2.0	
Electrical	
Power Consumption (W):	
8 (External Power Supply) 8.5 (PoE)	
Hardware & Interface Connectivity	
Interface:	
5GigE (PoE)	
Connector:	
5GigE, M12	
Power Supply:	
Power over Ethernet (PoE) or via GPIO with 12-24VDC Power Supply	
GPIOs:	
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports	
Synchronization:	
Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)	
Interface Port Orientation:	
Back Panel	
GPIO Connector Type:	
8-pin MB	
Threading & Mounting	
Mount:	
No Lens Mbunt	
Mounting Threads:	
¼-20 with Tripod Mbunt Adapter #13-751	
Environmental & Durability Factors	
Operating Temperature (°C):	
-20 to +55	
Storage Temperature (°C):	
-30 to +60	

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- 5GBASE-T (5GigE) Ethernet Interface
- 2.8 to 31.4 Megapixel Sensors
- Compact 55 x 55 x 70mm Design
- TFL-Mount Compatible with [TECHSPEC® CA Series FFL Lenses](#)

LUCID Vision Labs Atlas™ Power over Ethernet (PoE) 5GBASE-T (5GigE) Cameras have a small footprint and feature large format, high resolution sensors with up to 31.4MP at 17.9fps. During manufacturing, their imaging sensors are actively aligned to minimize sensor tilt and rotation, resulting in sharp and crisp images even in the corners. The 5GigE Ethernet interface provides up to 5X faster speeds than GigE for applications requiring high bandwidth. These cameras also feature a TFL-Mount that is easily adaptable to F-Mount. LUCID Vision Labs Atlas Power over Ethernet (PoE) 5GBASE-T (5GigE) Cameras are ideal for industrial applications including [factory automation](#), autonomous robotics, and biometrics.