

## M16 x 1.0 Female to 1/4-20 Male



Stock #55-208 **8 In Stock**

⊖ 1 ⊕ A\$32.80

**ADD TO CART**

### Volume Pricing

Qty 1-9	A\$32.80 each
Qty 10-24	A\$29.52 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

English/Metric **Type:**

### Physical & Mechanical Properties

20.00 **Diameter (mm):**

0.787 **Diameter (inches):**

0.472 **Length excluding Threads (inches):**

12.00	<b>Length excluding Threads (mm):</b>
0.67	<b>Total Length (inches):</b>
17	<b>Total Length (mm):</b>

## Threading & Mounting

<b>Mounting Threads:</b>	
Male: 1/4-20	
Female: M16 x 1.0	

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Male to Female Thread Design
- Ideal for Mating Optical Mounts and Components
- For use with 1/4-20 or M6 Breadboard Applications

Thread-To-Thread Adapters are key components when building a Benchtop Optical System. Optomechanic components feature a wide range of threads, so these adapters are an important addition to any optical lab space. M6 to 1/4"-20 adapters are used to change between English and metric configurations whereas 8-32 to 1/4"-20 adapters and Thread-To-Thread Adapters for M16 x 1.0 threaded components are ideal for a variety of mounting systems including our [Leadscrew Drive Stages](#) and [Metric Rotary Stages](#). For male to male thread adapters designed for out [TECHSPEC® Optical Mounting Posts](#), please use [TECHSPEC® Thread Adapters](#).

Thread-to-thread adapters offer versatile connection solutions for seamlessly integrating English, Metric, or mixed-thread components within optical assemblies. These adapters are constructed for durability and accommodate a range of mounting requirements, from lightweight setups to more robust mechanical stages. Whether adapting between 8-32, 1/4"-20, M6, or M16 threads, they simplify system modifications and ensure stability for demanding benchtop configurations. They are ideal for both prototyping and permanent installations where adaptability and mechanical integrity are critical.

### FAQ(s)

- What materials are used in the Thread-to-Thread Adapters?**  
The adapters are made from precision-machined metals to ensure durability, stability, and long-term mechanical performance in optical systems.
- Can I adapt between Metric and English thread types?**  
Yes, adapters such as M6 x 1.0 to 1/4"-20 allow seamless integration between Metric and English thread standards in optical setups.
- Are these adapters compatible with high-load applications?**  
Yes, they are designed to maintain strong, reliable connections, suitable for both lightweight optics and heavier mechanical stage assemblies.
- How critical are these adapters for building flexible optical systems?**  
Thread adapters are essential for expanding system compatibility, allowing users to repurpose or upgrade optical setups without major redesigns.

## Technical Information

A - Female Thread	B - Male Thread	C	D	E	Stock No.
1/4-20 x 0.25"L	M6-1.0 x 0.25"L	0.375"	0.38"	0.63"	<a href="#">#53-927</a>
M6-1.0 x 0.25"L	1/4-20 x 0.25"L	0.375"	0.38"	0.63"	<a href="#">#53-928</a>
8-32 x 0.2"L	1/4-20 x 0.25"L	0.250"	0.33"	0.58"	<a href="#">#53-929</a>
1/4-20 x 0.25"L	8-32 x 0.2"L	0.375"	0.38"	0.58"	<a href="#">#53-930</a>
M16-1.0 x 0.25"L	M6-1.0 x 0.25"L	30mm	10mm	15mm	<a href="#">#55-453</a>
M6-1.0 x 0.2"L	M16-1.0 x 0.2"L	20mm	6mm	11mm	<a href="#">#55-036</a>
M16-1.0 x 0.2"L	1/4-20 x 0.2"L	20mm	12mm	17mm	<a href="#">#55-208</a>