

M37.0 x 0.75 Thread, Ring Light Filter Thread Adapter



Ring Light Filter Thread Adapter. Filter Thread varies by Stock Number. (M30.5 x 0.5 Thread Shown)

Stock **#56-091** CLEARANCE **2 In Stock**

-

1

+

A\$73⁶⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$73.60 each
Need More?	Request Quote

Product Downloads

General

	Type of Illumination:
Accessory	

Physical & Mechanical Properties

	Construction:
Anodized Aluminum	

Threading & Mounting

	Filter Thread:
M37.0 x 0.75	

Regulatory Compliance		
Compliant	RoHS 2015:	
View	Certificate of Conformance:	
Compliant	Reach 235:	

Product Details

- Compatible with LED Ring Lights
- Common Filter Thread Sizes Available
- Allows for Easy Integration of LED Ring Lights

Ring Light Filter Thread Adapters allow our LED ring lights to connect directly to an [imaging lens](#). The adapter slides into a flange protruding from the back of the ring light. Select the ring light adapter with the threading that matches the front filter threading of the lens. All feature an anodized aluminum construction.

Note: Though Ring Light Filter Thread Adapters can work with a wide range of imaging lenses, the working distance and field coverage provided by the LED ring light must be considered. Vignetting may occur on very wide angle imaging lenses.

Technical Information

Filter Thread	Imaging Lenses Available to Use with Adapters	Adapter Stock No.
M25.5 x0.5	8.5/12/16/25/35/50/75mm C Series Fixed Focal Length Lenses	#56-523
M30.5 x0.5	18mm and 25mm DG Series FFL , 28mm Rodagon , MegaPixel Fixed Focal Length (vignetting may occur with large format sensors), Compact VIS-NIR Lenses (vignetting may occur with large format sensors)	#56-089
M34.5 x0.5	3.3X Macro Zoom Lens	#56-090
M37 x0.75	MMS® , 35mm DG Series FFL , 0.50X and 1.0X SilverTL™ Telecentric	#56-091
M39 x0.5	50mm DG Series FFL	#56-092
M40.5 x0.5	7X Close Focus Zoom (vignetting may occur with large format sensors or at lowest zoom settings), 35/50/60/80/105/135mm Rodagon Lenses , 0.60X SilverTL™ Telecentric Lenses	#56-093
M43 x0.75	55mm Telecentric , 0.30X/0.40X/2.0X SilverTL™ Telecentric	#56-094
M46 x0.75	10X Close Focus Zoom (vignetting may occur with large format sensors or at lowest zoom settings), 0.25X SilverTL™ Telecentric	#56-095
M49 x0.75	75mm DG Series FFL	#56-096
M52 x0.75	6X Close Focus Zoom (vignetting may occur with large format sensors or at lowest zoom settings), TECHSPEC® LS Series Fixed Focal Length Lenses	#56-097
M58 x0.75	0.36X/0.5X GoldTL™ Telecentric , 0.20X/4.0X SilverTL™ Telecentric	#56-098
M62 x0.75	0.73X/1X GoldTL™ Telecentric , 0.16X SilverTL™ Telecentric	#56-099
M72 x0.75	0.18X/0.25X GoldTL™ Telecentric	#56-100

Compatible Ring Lights	
Advanced Illumination Standard Working Distance LED Ring Lights	
Advanced Illumination Extended Working Distance LED Ring Lights	
Advanced Illumination Brightfield/Darkfield LED Ring Lights	
Advanced Illumination 5" Darkfield LED Illuminators	