

## Nikon 200mm Tube Lens

See More by [Nikon](#)



#58-520: Nikon 200mm Tube Lens

Stock **#58-520** **20+ In Stock**

-

1

+

A\$960<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | A\$960.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

|               |           |
|---------------|-----------|
| Type:         | Tube Lens |
| Manufacturer: | Nikon     |

Physical & Mechanical Properties

|                        |       |
|------------------------|-------|
| Length (mm):           | 29.00 |
| Maximum Diameter (mm): | 36.0  |

Optical Properties

|                       |        |
|-----------------------|--------|
| Focal Length FL (mm): | 200.00 |
|-----------------------|--------|


|                       |                               |
|-----------------------|-------------------------------|
| 1X                    | Magnification:                |
| 400 - 700             | Wavelength Range (nm):        |
| 26.5                  | Field Number (mm):            |
| 32.0                  | Entrance Pupil Diameter (mm): |
| Threading & Mounting  |                               |
| M38 x 0.5             | Mounting Threads:             |
| Regulatory Compliance |                               |
| Compliant             | RoHS 2015:                    |
| View                  | Certificate of Conformance:   |

Product Details

• Superior UV Transmission  
• High Numerical Aperture Designs  
• Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

Technical Information



| Dimensions (mm) |               |                  |      |      |      |         |
|-----------------|---------------|------------------|------|------|------|---------|
| Stock No.       | Magnification | Parafocal Length | A    | B    | C    | D       |
| #88-374         | 4X            | 60.06            | 30.0 | 44.4 | 19.7 | M25 x 0 |
| #88-375         | 10X           | 60.06            | 32.0 | 58.7 | 8.0  | M25 x 0 |
| #88-376         | 20X           | 60.06            | 33.5 | 58.9 | 9.0  | M25 x 0 |
| #88-377         | 40X           | 60.06            | 33.0 | 59.6 | 7.5  | M25 x 0 |