

[See all 21 Products in Family](#)

# Oryx® ORX-10G-245S8M Mono 10GigE

See More by [Teledyne FLIR](#)



ORYX-10G-310S9C



Stock #20-252 [CONTACT US](#)

- 1 + A\$7,640<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$7,640.00 each
Need More?	<a href="#">Request Quote</a>

Note: This item requires accessories for use | [Learn More](#)

## Product Downloads

Monochrome

Spectrum:

## General

Monochrome Camera

Type:

ORX-10G-245S8M

Model Number:

FLIR

Manufacturer:

Oryx®

Camera Series:

## Physical & Mechanical Properties

60 x 60 x 115

Dimensions (mm):

508

Weight (g):

Full

Housing:

## Sensor

240MB

Image Buffer:

1.2"

Sensor Format:

24.60

Resolution (Megapixels):

44.00

Frame Rate (fps):

5,320 x 4,600

Pixels (H x V):

2.74 x 2.74

Pixel Size, H x V (µm):

14.58 x 12.61

Sensing Area, H x V (mm):

Sony IMX530

Imaging Sensor:

Progressive Scan CMOS

Type of Sensor:

Global

Shutter Type:

12 bit

Pixel Depth:

7µs - 30s

Exposure Time:

70.48

Dynamic Range (dB):

GigE Vision

Machine Vision Standard:

## Electrical

13.8

Power Consumption (W):

## Hardware & Interface Connectivity

10GigE

Interface:

GigE interface with Screw Locks

Connector:

Power Supply:

Power Supply Required and Sold Separately.

USA: [#19-803](#)

Europe: [#19-803](#)

Japan: [#19-803](#)

Korea: Not Available

China: [#19-803](#)

GPIOs:

2 opto-isolated inputs, 2 opto-isolated outputs, 2 non-isolated bi-directional

**Synchronization:**  
Hardware Trigger (GPIO) or Software Trigger

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
12-pin Hirose (HR10)

## Threading & Mounting

**Mount:**  
F-Mount (With #20-256)

**Mounting Threads:**  
Built-in 1/4-20 Tripod Mount Adapter

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +50

**Storage Temperature (°C):**  
-30 to +60

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



Teledyne  
Authorized  
Distributor

### Teledyne FLIR IIS Oryx 10GigE: High throughput, Award-winning camera designs

Reliably capture images at high speed

The **Oryx 10GigE** camera family supports transfer speeds of up to 10 Gbit/s enabling capture of 4K resolution, 12-bit images at speeds exceeding 60 FPS. Reliable image transfer at high bandwidth is further improved with Myricom bundles and packet resend feature. A range of sensor options offer resolutions from 3.2 Megapixel up to 31 Megapixel.

Oryx features include IEEE1588 clock synchronization and full compatibility with several popular third-party software supporting GigE Vision. Oryx's 10GBASE-T interface is a proven and widely deployed standard that provides reliable image transfer at cable lengths over 50 meters on inexpensive CAT6A and up to 30 meters on CAT5e.

**Note:** The ORX-10G-310S9 and ORX-10G-245S8 cameras require an F-Mount lens adapter (sold separately).

#### Features

- Color or monochrome sensors
- Various frame triggering options including up to 8 sets of 2-feature sequencer
- Pixel binning, decimation, ROI
- On camera image processing includes Gamma, LUT, and sharpness

#### Applications

- Stadium venues
- Site security
- Factory automation
- Traffic monitoring
- Inspection systems