

Scratch & Dig Target (1st Surface Positive)



Scratch & Dig Target (1st Surface Positive), #59-154

Stock **#59-154** **3 In Stock**

1 **A\$1,840⁰⁰**

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | A\$1,840.00 each |
| Need More? | Request Quote |

Product Downloads

General

Note:
Standards are for comparing optics against ISO 10110 specifications.

Physical & Mechanical Properties

Every 0.025 **Scale Divisions:**
60 ±0.002 **Scale Length (mm):**
50.80 **Width (mm):**

| | |
|---------------------------------|-------------------------------------|
| 1.50 | Thickness (mm): |
| ±0.002 | Dot Diameter Tolerance (mm): |
| ±0.002 | Line Width Tolerance (mm): |
| Black Anodized Aluminum Housing | Construction: |
| ±0.2 | Housing Tolerance (mm): |
| 114.30 | Length (mm): |

Optical Properties

| | |
|----------------------------|--------------------------------|
| Float Glass | Substrate: □ |
| 3-4λ/Inch | Surface Flatness (P-V): |
| 20-10 (inside active area) | Surface Quality: |
| 45.00 | Angle of Incidence (°): |

Regulatory Compliance

| | |
|---------------------------|------------------------------------|
| Compliant | RoHS 2015: |
| Compliant | Reach 209: |
| View | Certificate of Conformance: |


Product Details

- Feature Requirements in Accordance with ISO 10110-7 & ISO 14997
- First Surface Pattern for System Calibration or Coating Inspection
- Second Surface Pattern for Measuring Surface Defects

NIST Traceable Scratch Dig Standards are ideal for qualifying the scratch and dig surface defects on optical components. In addition to the Scratch Dig markings, there is a 60mm scale, 6 grids varying in size, and 6 blocks of lines with varying frequencies on each plate. The grids can be used to measure the area of irregularly shaped defects. For the NIST Traceable Scratch Dig Standards, the square root of the total defect area for a region is the grade number for that region. The standards are offered as sets of two plates. Plate 1 includes grade numbers ranging from 0.004 to 0.040, while Plate 2 includes 0.040 to 0.400. The first surface sets have the features marked on the top of the glass substrate. The second surface set has the features marked on the bottom of the glass substrate. The features on the positive set are opaque on a clear background. The features on the negative set are clear on an opaque background.

Note: Certificate of Compliance is included with each product.

Technical Information



Units: mm

| Grade No. | Circ. Diameter (μm) | Dim. of Scratch (μm) | Freq. Block (lp/mm) | Grid Block Line W (μm) | Grid Block Line Spacing (μm) |
|-----------|---------------------|----------------------|---------------------|------------------------|------------------------------|
| 0.004 | 4.5 | 1 x 16 | 500 | 1 | 4.5 |
| 0.006 | 7 | 1.6 x 25 | 312.5 | 1.6 | 7 |
| 0.010 | 11 | 2.5 x 40 | 200 | 2.5 | 11 |
| 0.016 | 18 | 4 x 63 | 125 | 4 | 18 |
| 0.025 | 28 | 6.3 x 100 | 80 | 6.3 | 28 |
| 0.040 | 45 | 10 x 160 | 50 | 10 | 45 |

| Grade No. | Circ. Diameter (μm) | Dim. of Scratch (μm) | Freq. Block (lp/mm) | Grid Block Line W (μm) | Grid Block Line Spacing (μm) |
|-----------|---------------------|----------------------|---------------------|------------------------|------------------------------|
| 0.040 | 45 | 10 x 160 | 50 | 10 | 45 |

| | | | | | |
|-------|-----|------------|-------|----|-----|
| 0.060 | 70 | 16 x 225 | 31.25 | 10 | 70 |
| 0.100 | 110 | 25 x 400 | 20 | 10 | 110 |
| 0.160 | 180 | 40 x 630 | 12.5 | 10 | 180 |
| 0.250 | 280 | 63 x 1000 | 8 | 10 | 280 |
| 0.400 | 450 | 100 x 1600 | 5 | 10 | 450 |

;