

[See all 33 Products in Family](#)

TECHSPEC® UV-NIR, 12.5mm Diameter ND Filter Kit



Stock #88-368 [CONTACT US](#)

1 [+](#) [-](#) A\$1,112.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | A\$1,112.00 each |
| Need More? | Request Quote |

Product Downloads

General

[0.3, 0.5, 1.0, 1.3, 1.5, 2.0](#)

Filters Included :

Neutral Density Filter

Type:

6.00

Number of Filters:

Optical Properties

[Fused Silica](#) (Coming 7980)

Substrate:

Coating:

190 - 1700 **Blocking Wavelength Range (nm):**

0.19 - 1.7 **Wavelength Range (µm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details


UV-NIR Neutral Density Filter kit includes all optical densities. Filter coating is fragile and should be handled with care. Use non-contact cleaning methods only.

- Constant Transmission from 190 – 1700nm
- Can be Stacked to Create Intermediate Density Values
- Multiple Optical Densities Available

TECHSPEC® UV-NIR Neutral Density (ND) Filters are used to attenuate light from the ultraviolet to the near-infrared. TECHSPEC® UV-NIR ND Filters feature excellent parallelism with superior surface characteristics to provide constant, ultra-broadband performance from 190 – 1700nm. These ND filters are ideal for a range of applications including spectroscopy, machine vision, or ellipsometry, or for use with low power lasers. TECHSPEC® UV-NIR Neutral Density (ND) Filters can be stacked to obtain a range of optical densities.

Note: UV-NIR Neutral Density Filter kit includes all optical densities. Filter coating is fragile and should be handled with care. Use non-contact cleaning methods only.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools