

**CONTACT US**

**A\$1,112<sup>.00</sup>**

[ADD TO CART](#)

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | <b>A\$1,112.00</b> each       |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

| General |  |
|---------|--|
|---------|--|

**Filters Included :**

Type:

Number of Filters:

[illegible]Substrate: ☐

**Coating:**

|                   |                                 |
|-------------------|---------------------------------|
| Metallic Based ND |                                 |
| 190 - 1700        | Blocking Wavelength Range (nm): |
| 0.19 - 1.7        | Wavelength Range (µm):          |

Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details


UV-NIR Neutral Density Filter kit includes all optical densities. Filter coating is fragile and should be handled with care. Use non-contact cleaning methods only.

- Constant Transmission from 190 – 1700nm
- Can be Stacked to Create Intermediate Density Values
- Multiple Optical Densities Available

TECHSPEC® UV-NIR Neutral Density (ND) Filters are used to attenuate light from the ultraviolet to the near-infrared. TECHSPEC® UV-NIR ND Filters feature excellent parallelism with superior surface characteristics to provide constant, ultra-broadband performance from 190 – 1700nm. These ND filters are ideal for a range of applications including spectroscopy, machine vision, or ellipsometry, or for use with low power lasers. TECHSPEC® UV-NIR Neutral Density (ND) Filters can be stacked to obtain a range of optical densities.

**Note:** UV-NIR Neutral Density Filter kit includes all optical densities. Filter coating is fragile and should be handled with care. Use non-contact cleaning methods only.

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools